

NH-4

Mass 30g

The pins of the electrodes

in the tube with 2 plates:

- 1-figure 4
- 2-figure 6
- 3-figure 8
- 4-screen
- 5-figure 9
- 6-figure 7
- 7-is not connected
- 8-figure 0
- 9-figure 2
- 10-second plate
- 11-figure 3
- 12-figure 5
- 13-first plate
- 14-figure 1

in the tube with 1 plate :

- 1-figure 4
- 2-figure 6
- 3-figure 8
- 4- is not connected
- 5-figure 9
- 6-figure 7
- 7-is not connected
- 8-figure 0
- 9-figure 2
- 10- is not connected
- 11-figure 3
- 12-figure 5
- 13- plate
- 14-figure 1

Technical specifications:

Brightness $\geq 100\text{Kd/m}^2$

Power supply voltage $\geq 200\text{V}$

Lighting voltage $\leq 170\text{V}$

Operating voltage $\leq 160\text{V}$

The voltage of indication $\leq 2.5\text{mA}$

The operation voltage 2.5-3mA

Capacity of work $\geq 1000\text{hours}$

